



## HOLEX Pro Drill indexable drill Combination shank, 4xD, Ø DC: 24mm



### Order data

Order number	235010 24
GTIN	4062406253523
Item class	22L

### Description

**Version:**

HOLEX Pro Drill indexable drills combine cost efficiency with technically fully developed capability.

For use up to 4xD in challenging drilling applications.

**Bore tolerance:** -0.05 / +0.3 mm

**Application:**

With indexable inserts No. 235030 – 235082.

Both SOMT inserts for the outer insert seat and also XOMT inserts for the inner insert seat are required.

**Supplied with:**

With insert screws (supplied without indexable inserts).

**Recommendation:**

When spot-drilling reduce the feed rate to 70%.

### Technical description

Shank Ø D <sub>s</sub>	32 mm
ISO code indexable insert	SOMT093608 / XOMT093605

Nominal $\varnothing$ D	24
Reach $L_1$	99 mm
Pack of insert screws	232980 4 (TX9;1.2Nm)
Shank length $L_s$	60 mm
Series	HOLEX Pro
Number of cutting edges Z	1
Overall length L	181 mm
Maximum adjustment limit $V_{max}$	0.3 mm
Overhang $L_A$	121 mm
Drill depth for indexable insert drill up to	4xD
Shank	ISO 9766
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Use for drilling	limited oblique spot drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited drilling with oblique exit
Use for drilling	limited convexity
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

## Accessories

6 mm blade for Torx® Torx® profile TX9	659922 TX9
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200