

**HOLEX Pro Drill indexable drill Combination shank, 4xD, Ø DC: 24,5mm****Order data**

Order number	235010 24,5
GTIN	4062406253530
Item class	22L

Description**Version:**

HOLEX Pro Drill indexable drills combine cost efficiency with technically fully developed capability.

For use up to 4xD in challenging drilling applications.

Bore tolerance: -0.05 / +0.3 mm

Application:

With indexable inserts No. 235030 – 235082.

Both SOMT inserts for the outer insert seat and also XOMT inserts for the inner insert seat are required.

Supplied with:

With insert screws (supplied without indexable inserts).

Recommendation:

When spot-drilling reduce the feed rate to 70%.

Technical description

Shank length L _s	60 mm
Series	HOLEX Pro

Number of cutting edges Z	1
Nominal \varnothing D	24.5
Shank \varnothing D _s	32 mm
Reach L ₁	99.5 mm
Pack of insert screws	232980 4 (TX9;1.2Nm)
ISO code indexable insert	SOMT093608 / XOMT093605
Overall length L	181 mm
Maximum adjustment limit V _{max}	0.3 mm
Overhang L _A	121 mm
Drill depth for indexable insert drill up to	4×D
Shank	ISO 9766
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Use for drilling	limited oblique spot drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited drilling with oblique exit
Use for drilling	limited convexity
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

Accessories

6 mm blade for Torx® Torx® profile TX9	659922 TX9
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200