



HOLEX Pro Drill indexable drill Combination shank, 2xD, Ø DC: 19mm



Order data

Order number	235000 19
GTIN	4062406252793
Item class	22L

Description

Version:

HOLEX Pro Drill indexable drills combine cost efficiency with technically fully developed capability.

For use up to 4xD in challenging drilling applications.

Bore tolerance: -0.1 / +0.25 mm

Application:

With indexable inserts No. 235030 – 235082.

Both SOMT inserts for the outer insert seat and also XOMT inserts for the inner insert seat are required.

Supplied with:

With insert screws (supplied without indexable inserts).

Technical description

Series	HOLEX Pro
Reach L ₁	41 mm
Nominal Ø D	19
Shank Ø D _s	25 mm
ISO code indexable insert	SOMT06T205 / XOMT06T204
Number of cutting edges Z	1
for inch Ø	3/4 in
Pack of insert screws	232980 2 (TX7;0.8Nm)

Shank length L_s	56 mm
Overall length L	114 mm
Maximum adjustment limit V_{max}	0.25 mm
Overhang L_A	58 mm
Drill depth for indexable insert drill up to	2×D
Shank	ISO 9766
Use for drilling	limited centre drilling
Use for drilling	limited cross-drilling
Use for drilling	limited drilling with oblique exit
Use for drilling	limited oblique spot drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited convexity
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

Accessories

6 mm blade for Torx® Torx® profile TX7	659922 TX7
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200