



HOLEX Pro Drill indexable drill Combination shank, 2xD, Ø DC: 35mm



Order data

Order number	235000 35
GTIN	4062406252977
Item class	22L

Description

Version:

HOLEX Pro Drill indexable drills combine cost efficiency with technically fully developed capability.

For use up to 4xD in challenging drilling applications.

Bore tolerance: -0.1 / +0.25 mm

Application:

With indexable inserts No. 235030 – 235082.

Both SOMT inserts for the outer insert seat and also XOMT inserts for the inner insert seat are required.

Supplied with:

With insert screws (supplied without indexable inserts).

Technical description

Shank Ø D _s	32 mm
Pack of insert screws	232980 5 (TX15;3Nm)
Number of cutting edges Z	1
Reach L ₁	73 mm
Shank length L _s	60 mm
Nominal Ø D	15
Series	HOLEX Pro
for inch Ø	1 3/8 in

ISO code indexable insert	SOMT1 10408 / XOMT1 10406
Overall length L	157 mm
Maximum adjustment limit V_{\max}	0.35 mm
Overhang L_A	101 mm
Drill depth for indexable insert drill up to	2×D
Shank	ISO 9766
Use for drilling	limited centre drilling
Use for drilling	limited cross-drilling
Use for drilling	limited drilling with oblique exit
Use for drilling	limited oblique spot drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited convexity
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

Accessories

6 mm blade for Torx® Torx® profile TX15	659922 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500