



## HOLEX Pro Drill indexable drill Combination shank, 3xD, Ø DC: 32mm



### Order data

Order number	235005 32
GTIN	4062406253288
Item class	22L

### Description

#### Version:

HOLEX Pro Drill indexable drills combine cost efficiency with technically fully developed capability.

For use up to 4xD in challenging drilling applications.

**Bore tolerance:** -0.1 / +0.25 mm

#### Application:

With indexable inserts No. 235030 – 235082.

Both SOMT inserts for the outer insert seat and also XOMT inserts for the inner insert seat are required.

#### Supplied with:

With insert screws (supplied without indexable inserts).

### Technical description

Reach $L_1$	99 mm
Shank $\varnothing D_s$	32 mm
Pack of insert screws	232980 5 (TX15;3Nm)
ISO code indexable insert	SOMT110408 / XOMT110406
Series	HOLEX Pro
Shank length $L_s$	60 mm
Nominal $\varnothing D$	32
Number of cutting edges Z	1

Overall length L	186 mm
Maximum adjustment limit $V_{\max}$	0.35 mm
Overhang $L_A$	126 mm
Drill depth for indexable insert drill up to	3×D
Shank	ISO 9766
Use for drilling	limited drilling through a stack
Use for drilling	limited convexity
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Use for drilling	limited oblique spot drilling
Use for drilling	limited drilling with oblique exit
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

## Accessories

6 mm blade for Torx® Torx® profile TX15	659922 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500