



Vernier caliper with mm and inch graduations, Measuring range: 300mm



Order data

Order number	415120 300
GTIN	4062406253776
Item class	41Z

Description

Version:

Chamfered measuring tips for measurements to the root of threads and in narrow grooves. Offset and rounded jaw ends for internal measurements. High-contrast scale. With locking screw. Up to size 300 through hardened, from size 500 measuring faces hardened.

Technical description

Calibration	A1
Measuring range	0 - 300 mm
Jaw length	90 mm
Packaging	sturdy box
Internal jaw \varnothing	10 mm
Graduation	1/128 in
Graduation	1/50 mm
Standard	ISO 13385
Measurement deviation E MPE	± 0.04 mm
Vernier graduations mm/inch	yes
Measuring tips	yes
Measurement technology	analogue

Material	Stainless steel, INOX
Type of product	Workshop calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300
CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300