

**Vernier caliper with mm and inch graduations, Measuring range: 500mm****Order data**

Order number	415120 500
GTIN	4062406253783
Item class	41Z

**Description****Version:**

Chamfered measuring tips for measurements to the root of threads and in narrow grooves. Offset and rounded jaw ends for internal measurements. High-contrast scale. With locking screw. Up to size 300 through hardened, from size 500 measuring faces hardened.

**Technical description**

Standard	ISO 13385
Calibration	A1
Packaging	sturdy box
Measuring range	0 - 500 mm
Graduation	1/128 in
Graduation	1/50 mm
Jaw length	150 mm
Internal jaw $\varnothing$	20 mm
Measurement deviation E MPE	$\pm 0.05$ mm
Vernier graduations mm/inch	yes
Measuring tips	yes
Measurement technology	analogue

Material	Stainless steel, INOX
Type of product	Workshop calipers

**Services**

DAkkS calibrationCalipers / depth gauges maximum measuring range 500 mm	021010 500
CalibrationCalipers / depth gauges maximum measuring range 500 mm	021000 500