

Garant**Hydraulic arbor VDI 30, VDI 30, ØD1: 20mm****Order data**

Order number	319753 20
GTIN	4062406254490
Item class	31M

Description**Version:**

Unique clamp bridging, clamps h6 and h7 shanks. Laser finished on the end face and alignment screw on the bracket, for simple and clear orientation of the boring bar. Including length adjustment backstop screw. Suitable for through-coolant.

Two attachment screws for the best accessibility, be it at the headstock or tailstock. Supplied with ball spray nozzle.

Advantage:

- **Ideal damping characteristics, resulting in optimum component surfaces. and increased tool life.**
- **Quick and easy handling.**
- **Flexible use of reducing adapters.**
- **Perfect centring.**

Application:

Suitable for drilling, reaming, countersinking and also for use of boring bars.

Technical description

External Ø D	42 mm
Clamping Ø D ₁	20 mm
Weight	0.5 kg

Overhang dimension A	64 mm
Reach L ₁	42 mm
Adapter	VDI 30
Type of product	Hydraulic clamping chuck