

Garant**Hydraulic arbor Shank \varnothing 32 mm, \varnothing D1: 20mm****Order data**

Order number	319751 20
GTIN	4062406254520
Item class	31M

Description**Version:**

Unique clamp bridging, clamps h6 and h7 shanks. Laser finished on the end face and alignment screw on the bracket, for simple and clear orientation of the boring bar. Including length adjustment backstop screw. Suitable for through-coolant.

Flexible use on all types of turret.

Advantage:

- **Ideal damping characteristics, resulting in optimum component surfaces and increased tool life.**
- **Quick and easy handling.**
- **Flexible use of reducing adapters.**
- **Perfect centring.**

Application:

Suitable for drilling, reaming, countersinking and also for use of boring bars.

Technical description

\varnothing D ₂	41 mm
Overhang dimension A	19.5 mm
Thread M	M22×1
Reach L ₁	59 mm

Ø D ₃	32 mm
Clamping Ø D ₁	20 mm
Width B	50 mm
Type of product	Hydraulic clamping chuck