

Garant GRIDLINE

eLevel+ workstation with bamboo worktop, Length: 1000mm**Order data**

| | |
|--------------|---------------|
| Order number | 920026 1000 |
| GTIN | 4062406254940 |
| Item class | 91P |

Description**Version:**

Workstation eLevel+ height steplessly adjustable electrically. Height adjustment via an electronic control panel. Control panel with display and memory function. Push-button adjustment for a suitable worktop height.

Colour:

Support leg RAL 7016 anthracite, **not configurable**.

Lift columns anodised aluminium, **not configurable**.

Side panel and rear panel RAL 7035 light grey **powder-coated, configurable**.

Note:

- **If using casings attached to the underside of the worktop, note that such casings may not exceed a maximum height of 500 mm.**
- **Caution: when installing benches in a row, please use side plates no. 920350 (crush hazard).**

Sizes with .../2 are fitted with an alternative lift unit. Technical data is similar to the previous lift units, slight deviations. Control panel is visually different for these sizes, but functionally the same.

Technical description

| | |
|----------------------------|---------|
| Width | 1000 mm |
| Stepless height adjustment | yes |

| | |
|---|--|
| Height with rear panel | 1000 mm |
| Control panel with display and memory functions | yes |
| Series | Workstation |
| Principle of height adjustment | only with worktop |
| Weight | 78 kg |
| Material of worktop | Bamboo |
| Model | eLevel+ |
| Worktop length | 1000 mm |
| Height adjustment range (worktop surface) from – to | 700 - 1000 mm |
| Depth | 800 mm |
| Worktop thickness | 50 mm |
| Worktop depth | 700 mm |
| Plug type, input | F |
| Nominal voltage | 250 V |
| Height adjustment workstation | 700-1000 mm |
| Design version | Steel hollow section construction |
| Workbench/desk load capacity - maximum distributed load (on wood) | 250 kg |
| Type of height adjustment | electrical |
| Insert thickness | 50 mm |
| Height adjustment | 25 mm |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | Work table |

Accessories

Drawer casing, 16G mobile Casing height mm / number of drawers 500/4

927315 500/4

927315 500/3

Drawer casing, 16G mobile Casing height mm / number of drawers 500/3

Support columns Height 481 mm 928010 481

Drawer casing, 16G mobile Casing height mm / number of drawers 400/4 927315 400/4

Drawer casing 16G with drawers Height / number of drawers 400/4 927300 400/4

Drawer casing 24G with drawers Height / number of drawers 200/1 927600 200/1

Drawer casing 16G with drawers Height / number of drawers 300/3 927300 300/3

Side plate for workstations Suitable for workstation depth 800 mm 920350 800

Drawer casing 24G with drawers Height / number of drawers 300/2 927600 300/2

Drawer casing, 24G mobile Casing height / number of drawers 500/5 mm 927620 500/5

Drawer casing 16G with drawers Height / number of drawers 400/3 927300 400/3

Support columns Height 1362 mm 928010 1362

Drawer casing, 16G mobile Casing height mm / number of drawers 500/5 927315 500/5

16G computer casing Height 500 mm 927335 500

Drawer casing 16G with drawers Height / number of drawers 300/2 927300 300/2

Drawer casing 24G with drawers Height / number of drawers 400/4 927600 400/4

Support columns Height 962 mm 928010 962

Drawer casing 24G with drawers Height / number of drawers 300/3 927600 300/3

Support columns Height 200 mm 928010 200

Drawer casing 24G with drawers Height / number of drawers 500/5 927600 500/5

Multifix suitable for type 300 928201 300

| | |
|------------------------|----------|
| PC holder Type M | 928753 M |
| Keyboard drawer Type 1 | 927341 1 |