

Garant GRIDLINE

eLevel workstation with bamboo worktop, Length: 2000mm



Order data

Order number	920016 2000
GTIN	4062406254926
Item class	91P

Description

Version:

Workstation eLevel height steplessly adjustable electrically. Height adjustment by an electronic control panel. Control panel with display and memory functions. Push-button adjustment for a suitable **height of the entire workstation**.

Colour:

Support leg RAL 7016 anthracite, **not configurable**.

Lift columns anodised aluminium, **not configurable**.

Side panel and rear panel RAL 7035 light grey **powder-coated, configurable**.

Note:

- **If using casings attached to the underside of the worktop, note that such casings may not exceed a maximum height of 500 mm.**
- **Caution: when installing benches in a row, please use side plates no. 920350 (crush hazard).**

Sizes with .../2 are fitted with an alternative lift unit. Technical data is similar to the previous lift units, slight deviations. Control panel is visually different for these sizes, but functionally the same.

Technical description

Principle of height adjustment	complete structure
Control panel with display and memory functions	yes
Weight	93 kg

Worktop thickness	50 mm
Material of worktop	Bamboo
Series	Workstation
Model	eLevel
Stepless height adjustment	yes
Height adjustment range (worktop surface) from – to	700 - 1000 mm
Worktop depth	700 mm
Width	2000 mm
Worktop length	2000 mm
Depth	800 mm
Nominal voltage	250 V
Plug type, input	F
Height adjustment workstation	700-1000 mm
Design version	Steel hollow section construction
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	electrical
Insert thickness	50 mm
Height adjustment	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

Accessories

Keyboard drawer Type 1	927341 1
Drawer casing 24G with drawers Height / number of drawers 300/2	927600 300/2
PC holder Type M	928753 M
	927600 500/5

Drawer casing 24G with drawers Height / number of drawers 500/5

Side plate for workstations Suitable for workstation depth 800 mm

920350 800

Support columns Height 1362 mm

928010 1362

Support columns Height 200 mm

928010 200

Drawer casing 24G with drawers Height / number of drawers 300/3

927600 300/3

16G computer casing Height 500 mm

927335 500

Multifix suitable for type 300

928201 300

Drawer casing 16G with drawers Height / number of drawers 300/3

927300 300/3

Drawer casing, 16G mobile Casing height mm / number of drawers 500/4

927315 500/4

Drawer casing 24G with drawers Height / number of drawers 400/4

927600 400/4

Drawer casing, 24G mobile Casing height / number of drawers 500/5 mm

927620 500/5

Support columns Height 481 mm

928010 481

Drawer casing, 16G mobile Casing height mm / number of drawers 500/3

927315 500/3

Drawer casing 16G with drawers Height / number of drawers 300/2

927300 300/2

Drawer casing 16G with drawers Height / number of drawers 400/4

927300 400/4

Drawer casing, 16G mobile Casing height mm / number of drawers 400/4

927315 400/4

Drawer casing 24G with drawers Height / number of drawers 200/1

927600 200/1

Drawer casing, 16G mobile Casing height mm / number of drawers 500/5

927315 500/5

Support columns Height 962 mm

928010 962

Drawer casing 16G with drawers Height / number of drawers 400/3

927300 400/3

