

Garant GRIDLINE

mLevel workstation with bamboo worktop, Length: 1500mm



Order data

Order number	920006 1500
GTIN	4062406254872
Item class	91P

Description

Version:

Workstation mLevel, the workstation that adapts to your needs. Classic manual height adjustment in 25-mm steps using a support leg with securing bolts by which the height of the entire workstation is adjusted. Scaling on the inside of the table showing the exact working height for ease of operation.

Colour:

Support leg RAL 7016 anthracite, **not configurable**.

Lift columns anodised aluminium, **not configurable**.

Side panel and rear panel RAL 7035 light grey **powder-coated, configurable**.

Technical description

Material of worktop	Bamboo
Stepless height adjustment	no
Height adjustment range (worktop surface) from – to	750 - 1000 mm
Series	Workstation
Worktop length	1500 mm
Model	mLevel
Weight	70 kg
Width	1500 mm

Principle of height adjustment	complete structure
Worktop thickness	50 mm
Control panel with display and memory functions	no
Worktop depth	700 mm
Depth	800 mm
Height adjustment workstation	750-1000 mm
Design version	Steel hollow section construction
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	mechanical
Insert thickness	50 mm
Height adjustment	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

Accessories

Cleaner and care oil set Type 1	926403 1
Drawer casing 24G with drawers Height / number of drawers 400/4	927600 400/4
Drawer casing 16G with drawers Height / number of drawers 400/3	927300 400/3
Support columns Height 1362 mm	928010 1362
Drawer casing 24G with drawers Height / number of drawers 500/5	927600 500/5
Drawer casing, 16G mobile Casing height mm / number of drawers 400/4	927315 400/4
Drawer casing 24G with drawers Height / number of drawers 300/3	927600 300/3
16G computer casing Height 500 mm	927335 500

Support columns Height 200 mm	928010 200
Drawer casing, 16G mobile Casing height mm / number of drawers 500/3	927315 500/3
Drawer casing 16G with drawers Height / number of drawers 300/3	927300 300/3
Support columns Height 481 mm	928010 481
Drawer casing, 16G mobile Casing height mm / number of drawers 500/4	927315 500/4
Drawer casing 16G with drawers Height / number of drawers 300/2	927300 300/2
Drawer casing, 24G mobile Casing height / number of drawers 500/5 mm	927620 500/5
PC holder Type M	928753 M
Keyboard drawer Type 1	927341 1
Support columns Height 962 mm	928010 962
Drawer casing, 16G mobile Casing height mm / number of drawers 500/5	927315 500/5
Multifix suitable for type 300	928201 300
Drawer casing 24G with drawers Height / number of drawers 200/1	927600 200/1
Drawer casing 16G with drawers Height / number of drawers 400/4	927300 400/4
Drawer casing 24G with drawers Height / number of drawers 300/2	927600 300/2