

Garant GRIDLINE

eLevel+ workstation with bamboo worktop, Length: 1500mm



Order data

Order number	920026 1500
GTIN	4062406254957
Item class	91P

Description

Version:

Workstation eLevel+ height steplessly adjustable electrically. Height adjustment via an electronic control panel. Control panel with display and memory function. Push-button adjustment for a suitable worktop height.

Colour:

Support leg RAL 7016 anthracite, **not configurable**.

Lift columns anodised aluminium, **not configurable**.

Side panel and rear panel RAL 7035 light grey **powder-coated, configurable**.

Note:

- **If using casings attached to the underside of the worktop, note that such casings may not exceed a maximum height of 500 mm.**
- **Caution: when installing benches in a row, please use side plates no. 920350 (crush hazard).**

Sizes with .../2 are fitted with an alternative lift unit. Technical data is similar to the previous lift units, slight deviations. Control panel is visually different for these sizes, but functionally the same.

Technical description

Model	eLevel+
Stepless height adjustment	yes

Depth	800 mm
Worktop thickness	50 mm
Width	1500 mm
Series	Workstation
Worktop length	1500 mm
Control panel with display and memory functions	yes
Weight	90 kg
Worktop depth	700 mm
Material of worktop	Bamboo
Height adjustment range (worktop surface) from – to	700 - 1000 mm
Height with rear panel	1000 mm
Principle of height adjustment	only with worktop
Nominal voltage	250 V
Plug type, input	F
Height adjustment workstation	700-1000 mm
Design version	Steel hollow section construction
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	electrical
Insert thickness	50 mm
Height adjustment	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

Accessories

Support columns Height 1362 mm	928010 1362
PC holder Type M	928753 M

Support columns Height 481 mm	928010 481
Drawer casing, 24G mobile Casing height / number of drawers 500/5 mm	927620 500/5
Drawer casing 16G with drawers Height / number of drawers 300/3	927300 300/3
Keyboard drawer Type 1	927341 1
Support columns Height 200 mm	928010 200
Drawer casing, 16G mobile Casing height mm / number of drawers 500/3	927315 500/3
Drawer casing 24G with drawers Height / number of drawers 300/3	927600 300/3
Drawer casing 16G with drawers Height / number of drawers 400/3	927300 400/3
Side plate for workstations Suitable for workstation depth 800 mm	920350 800
Drawer casing, 16G mobile Casing height mm / number of drawers 500/5	927315 500/5
Drawer casing, 16G mobile Casing height mm / number of drawers 500/4	927315 500/4
Multifix suitable for type 300	928201 300
Support columns Height 962 mm	928010 962
Drawer casing 16G with drawers Height / number of drawers 400/4	927300 400/4
Drawer casing 16G with drawers Height / number of drawers 300/2	927300 300/2
Drawer casing, 16G mobile Casing height mm / number of drawers 400/4	927315 400/4
Drawer casing 24G with drawers Height / number of drawers 500/5	927600 500/5
Drawer casing 24G with drawers Height / number of drawers 200/1	927600 200/1
Drawer casing 24G with drawers Height / number of drawers 300/2	927600 300/2
	927600 400/4

Drawer casing 24G with drawers Height / number of
drawers 400/4

16G computer casing Height 500 mm

927335 500