

Garant GRIDLINE

Corner module with bamboo worktop, Worktop length: 1000 mm**Order data**

Order number	920116 1000
GTIN	4062406254988
Item class	91P

Description**Version:**

Corner workstation for workstation. Simple version with fixing brackets of sheet metal, height-adjustable support, load capacity **150 kg**. Manual and electric height adjustment.

Suitable for :

Workstation mLevel, eLevel, eLevel+.

Colour:

Support leg RAL 7016 anthracite (not configurable), **side and back panels** RAL 7035 light grey, **powder-coated**.

Height adjustment range (worktop surface) from – to: 700 - 1000 mm

Width: 1000 mm

Depth: 800 mm

Worktop length: 1000 mm

Worktop depth: 1000 mm

Worktop thickness: 50 mm

Technical description

Worktop length	1000 mm
Tapering to worktop depth	800 mm

Weight	32 kg
Height adjustment range (worktop surface) from – to	700 - 1000 mm
Worktop depth	1000 mm
Series	Workstation
Principle of height adjustment	complete structure
Width	1000 mm
Worktop thickness	50 mm
Depth	800 mm
Design version	Steel hollow section construction
Height adjustment workstation	700-1000 mm
Workbench/desk load capacity - maximum distributed load (on wood)	150 kg
Type of height adjustment	mechanical
Insert thickness	50 mm
Height adjustment	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Corner solution for workbench

Accessories

Cleaner and care oil set Type 1	926403 1
---------------------------------	----------