

TAJIMA

**Tape measure with extra-strong protective casing, with magnetic end hook,
Band length: 5/25 m**

**Order data**

Order number	462338 5/25
GTIN	4975364028426
Item class	46R

Description**Version:**

Your sturdy G-Lock tape measure with **extra-strong protective casing**. Non-slip casing. Sliding end hook secured with 3 rivets. Automatic tape return and stop. Shock absorber reduces the impact at tape return. Easy to read scale on the front and back. Tape measure printed black/red on yellow, acrylic coated for high abrasion resistance. Supplied with belt clip.
with magnetic end hook.

Calibration: G1

Standard: EG II

Tape width: 25 mm

Body length: 67 mm

Body width: 28 mm

Body height: 63 mm

Technical description

Body length	67 mm
Body width	28 mm
Body height	63 mm
Tape width	25 mm

Standard	EG II
Calibration	G1
Type of product	Locking tape measure in a housing, capsule, frame

Services

Calibration Locking tape measure maximum length 5/2 m	016140 5/2
Labelling laser-etched Type	018940