

**TCMT 16T308, Grade: HBT130****Order data**

Order number	261019 HBT130
GTIN	4062406257545
Item class	22D

Description

TCMT 16T308 HBT130 Grade: HBT130
Chip breaker: MM
Cutting depth a_p : 0.3 - 2.5 mm
Feed f : 0.05 - 0.35 mm/rev.
Cutting speed v_c main application: 50 - 200 m/min

Technical description

Cutting depth a_p	0.3 - 2.5 mm
Coating	TiCN
Corner radius	0.8 mm
Grade	HBT130
Cutting speed v_c main application	50 - 200 m/min
Feed f	0.05 - 0.35 mm/rev.
Number of changes/inserts	3
Tool material	Carbide

Chip breaker	MM
Cutting conditions	slightly interrupted
ISO code indexable insert	TCMT 16T308
Main application	M
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Type of product	Indexable insert for turning