

**Toe clamp, Thread: M12****Order data**

Order number	375006 M12
GTIN	4059245237890
Item class	37K

Description**Version:**

Especially low-height and compact design. Pull-down effect due to oblique guidance wedge.

Application:

For lateral clamping of particularly flat components directly on the jig insert.

Material:

Quenched and tempered steel.

Technical description

Height H	38 mm
Clamping range	5 mm
Clamping force	20 kN
Height H ₁	23 mm
maximum tightening torque	90 Nm
Width B	35 mm

Material	Quenched and tempered steel.
Type of product	Side clamps