

**Toe clamp, Thread: M8****Order data**

Order number	375006 M8
GTIN	4059245237852
Item class	37K

Description**Version:**

Especially low-height and compact design. Pull-down effect due to oblique guidance wedge.

Application:

For lateral clamping of particularly flat components directly on the jig insert.

Material:

Quenched and tempered steel.

Technical description

Clamping force	7 kN
Height H	25 mm
maximum tightening torque	25 Nm
Material	Quenched and tempered steel.
Clamping range	3 mm
Width B	25 mm

Height H ₁	15 mm
Type of product	Side clamps