

**Toe clamp, Thread: M16****Order data**

Order number	375006 M16
GTIN	4059245237913
Item class	37K

Description**Version:**

Especially low-height and compact design. Pull-down effect due to oblique guidance wedge.

Application:

For lateral clamping of particularly flat components directly on the jig insert.

Material:

Quenched and tempered steel.

Technical description

Material	Quenched and tempered steel.
Width B	40 mm
Height H ₁	25 mm
Clamping force	40 kN
Clamping range	6 mm
Height H	45 mm

maximum tightening torque	200 Nm
Type of product	Side clamps