

**Toe clamp, Thread: M10****Order data**

Order number	375006 M10
GTIN	4059245237876
Item class	37K

Description**Version:**

Especially low-height and compact design. Pull-down effect due to oblique guidance wedge.

Application:

For lateral clamping of particularly flat components directly on the jig insert.

Material:

Quenched and tempered steel.

Technical description

Height H ₁	19 mm
Width B	30 mm
Height H	32 mm
Clamping range	4 mm
Clamping force	8.5 kN
maximum tightening torque	50 Nm

Material	Quenched and tempered steel.
Type of product	Side clamps