



## Stainless steel measuring tape for circumference and Ø Tape width 35 mm, maximum total measuring range: 4720mm



### Order data

Order number	465684 4720
GTIN	2050002041264
Item class	46R

### Description

#### Version:

Steel measuring tape **CJU** for measuring external circumferences and Ø of spherical bodies. The spring steel strip is laser scaled on the front with 2 scales, one for circumference and the other for Ø. Graduations 1 mm. **Vernier reading 0.1 mm**. Scale graduation error limits to DIN 866.

**V2A version** made of stainless spring steel.

#### Advantage:

Easy handling and centring capability thanks to broad contact face. Increased stability. Quicker and more reliable measuring.

#### Note:

Measuring tapes C with reading 0.05 mm and measuring tapes with black coating available on request. Fixed version CJU on request.

### Technical description

Tape thickness	0.2 mm
Scale divisions	0.1 mm
Measuring range for Ø	1100 - 1500 mm
Tape width	35 mm
Measuring range for circumferences	3450 - 4720 mm
Calibration	G2

Type of product

Measuring tape

**Services**CalibrationCircumference tape measure maximum length  
6000 mm

026280 6000