



Stainless steel measuring tape for circumference and \emptyset Tape width 35 mm, maximum total measuring range: 2200mm



Order data

Order number	465684 2200
GTIN	2050002041240
Item class	46R

Description

Version:

Steel measuring tape **CJU** for measuring external circumferences and \emptyset of spherical bodies. The spring steel strip is laser scaled on the front with 2 scales, one for circumference and the other for \emptyset . Graduations 1 mm. **Vernier reading 0.1 mm**. Scale graduation error limits to DIN 866.

V2A version made of stainless spring steel.

Advantage:

Easy handling and centring capability thanks to broad contact face. Increased stability. Quicker and more reliable measuring.

Note:

Measuring tapes C with reading 0.05 mm and measuring tapes with black coating available on request. Fixed version CJU on request.

Technical description

Tape thickness	0.2 mm
Scale divisions	0.1 mm
Tape width	35 mm
Measuring range for \emptyset	300 - 700 mm
Measuring range for circumferences	940 - 2200 mm
Calibration	G2

Type of product

Measuring tape

ServicesCalibrationCircumference tape measure maximum length
3000 mm

026280 3000