



Stainless steel measuring tape for circumference and \emptyset Tape width 35 mm, maximum total measuring range: 5980mm



Order data

Order number	465684 5980
GTIN	2050002041271
Item class	46R

Description

Version:

Steel measuring tape **CJU** for measuring external circumferences and \emptyset of spherical bodies. The spring steel strip is laser scaled on the front with 2 scales, one for circumference and the other for \emptyset . Graduations 1 mm. **Vernier reading 0.1 mm**. Scale graduation error limits to DIN 866.

V2A version made of stainless spring steel.

Advantage:

Easy handling and centring capability thanks to broad contact face. Increased stability. Quicker and more reliable measuring.

Note:

Measuring tapes C with reading 0.05 mm and measuring tapes with black coating available on request. Fixed version CJU on request.

Technical description

Measuring range for circumferences	4710 - 5980 mm
Tape thickness	0.2 mm
Scale divisions	0.1 mm
Tape width	35 mm
Measuring range for \emptyset	1500 - 1900 mm
Calibration	G2

Type of product

Measuring tape

ServicesCalibrationCircumference tape measure maximum length
6000 mm

026280 6000