

Garant**ESD plug-in extension rack, Depth 500 mm, Height: 2000mm****Order data**

Order number	972515 2000
GTIN	4062406256494
Item class	91I

Description**Version:**

Sturdy column frame of rectangular columns (50×25×1.25 mm) with slots at intervals of 40 mm for mounting cross beams / shelves. Column frames with non-conductive plastic end caps. No tools required for assembly. The high lateral stability eliminates the need for diagonal struts for stabilisation. Storage shelves are **ESD powder-coated**. A galvanised spring on the storage shelf ensure reliable contact with the installed earthing point.

Supplied with:

Includes ESD grounding cable.

Colour:

Light grey similar to RAL 7035 **ESD powder-coated**.

Note:

- **To ensure the stability of the racking, measures to prevent tipping are necessary where the height to depth ratio is greater than 5:1.**
- **All plastic components (e.g. covering caps) are not ESD conductive.**

Technical description

Storage shelf clear width	900 mm
---------------------------	--------

maximum bay load	900 kg
Assembled size basic rack width	975 mm
Shelf width	946 mm
Number of shelves	4
Shelf load capacity / maximum distributed shelf load (on metal)	120 kg
Shelf thickness	38 mm
Height adjustment interval	40 mm
electrostatic characteristic	EGB/ESD
Product name attribute	Depth 500 mm
Type of product	Storage shelf