

**Garant****Pole pieces, pair, for type: 300****Order data**

|              |               |
|--------------|---------------|
| Order number | 382025 300    |
| GTIN         | 4062406257804 |
| Item class   | 310           |

**Description****Version:**

Option 1

workpiece  $\varnothing$ : 40 – 300 mm

Option 2

workpiece  $\varnothing$ : 158 – 500 mm

Option 3

max. vertical load: 160 kg

**Description:****Option 1:** Workpiece diameter 40 – 300 mm.**Option 2:** Workpiece diameter 158 – 500 mm.**Option 3:** max. vertical load: 160 kg.**Application:**

For mounting on the pole face of the load lifter. This allows workpieces of different diameters to be lifted. Optimised accessibility for individual lifting situations.

**Suitable for:**

Lifting magnet LM1 No. 382020 size 300 and 600.

**Supplied with:**

Supplied with fastening screws and attachment pins for transporting vertical loads.

**Note:****Switch the load lifting magnets on only on magnetic surfaces!**

The maximum safe working load varies according to the option selected.

## Technical description

Type of product

Pole piece

---

## Accessories

LM1 lifting magnet maximum loading capacity (level) 300 kg

382020 300