

ESD SMD fittings set, Number of tools: 9**Order data**

Order number	973230 9
GTIN	2050002041950
Item class	91A

Description**Version:**

Popular tool selections in ESD foam inlay. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

ESD rigid foam inlay, empty No. 973200 size 973230: 1 pc.
GARANT ESD electronics side cutter No. 726210 size 125: 1 pc.
KNIPEX ESD electronics side cutter No. 726660 size 125: 1 pc.
GARANT ESD electronics snipe-nosed pliers No. 727170 size 140: 1 pc.
HOLEX ESD tweezers, pointed tips, No. 727520 size AMB: 1 pc.
HOLEX ESD tweezers, rounded tips, No. 727580 size AMB: 1 pc.
HOLEX ESD tweezers, narrow tips, No. 727600 size AMB: 1 pc.
Precision handle, without blade No. 845320: 1 pc.
Scalpel blades, pack of 12, No. 845330 size 18: 1 pc.
Protective cap for precision handle No. 845335: 1 pc.

Technical description

Depth	300 mm
Number of tools	9

Width in G	10
Depth in G	12
Width	250 mm
Version	with tool kit
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	10×12
electrostatic characteristic	EGB/ESD
Type of product	Rigid foam inlay

Accessories

Rigid foam inlay, empty, for tool setsESD suitable for rigid foam set 973230	973200 973230
Electronics side cutter Super Knips®, conductive grips overall length 125 mm	726660 125
Protective cap for No. 845320 / 5325	845335
Precision handle (without blade) of non-rusting stainless steel	845320
Electronics snipe-nosed pliers Overall length 140 mm	727170 140
Tweezers shouldered, flat tips 2.5 mm wide 120 mm, Form 2a Material AMB	727580 AMB
Scalpel blades set12 pieces Type 18	845330 18
Tweezers pointed, 125 mm Form AA Material AMB	727520 AMB
Tweezers with narrow tips angled, 150 mm, Form 22b Material AMB	727600 AMB
Electronics side cutter, standard head shape Overall length 125 mm	726210 125