

**LED torch, black with batteries, Type: 117****Order data**

Order number	081533 117
GTIN	4062406258412
Item class	02A

**Description****Version:**

High-quality, long-life and sturdy LED torch of anodised aluminium. **Latest LED technology** with **outstanding lighting power**.

- **Anti-roll protection.**
- **Rubber cover for the operating button.**

With **focussable** lamp head.

**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

**Technical description**

Torch function	Focus
Overall length	117 mm
Illumination time	5 h
ATEX zone	no

Battery type	Mignon, AA
Number of batteries contained	1
Illumination	160 lm
IP Index of Protection	IP 54
Power supply	Battery-powered
Type of product	Flashlight

---

## Accessories

Alkaline-manganese batteries International size LR6	081554 LR6
Alkaline-manganese batteries International size LR6	081561 LR6
Alkaline-manganese batteries International size LR6	081552 LR6
Alkaline-manganese batteries International size LR6	081553 LR6
Alkaline-manganese batteries International size LR6	081551 LR6
Lithium-metal batteries International size LR6	081559 LR6