

**BENNING****Phase and phase sequence tester Tritest Easy, Type: TRITEST****Order data**

|              |                |
|--------------|----------------|
| Order number | 473280 TRITEST |
| GTIN         | 4014651200517  |
| Item class   | 47A            |

**Description****Version:**

For quick and easy phase testing at sockets, junction boxes, switches and lamps. Locates cable breaks in insulated cables.

**Function:**

IP53: Protected against splashed water from directions up to 60° when in normal operating position and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

**Application:**

Additional phase sequence testing.

Phase testing, testing of insulated cables and testing for broken cables.

**Standard:**

**DIN EN 61010-1.**

**Supplied with:**

2 batteries No. 081561 size LR3.

**Technical description**

|   |                              |
|---|------------------------------|
| Overtoltage category                                    | CAT III 1000 V; CAT IV 600 V |
| Voltage range AC  | 200 - 1000 V                 |
| IP Index of Protection                                  | IP 53                        |
| Number of batteries contained                           | 2                            |
| Power supply  | Battery-powered              |
| Article no of the battery / rechargeable battery fitted | 081561 LR3                   |
| Material of the housing                                 | ABS plastic                  |

Type of product

Phase and phase sequence tester

---

## Accessories

Alkaline-manganese batteries International size LR3

081561 LR3