

STANLEY**Tape measure Powerlock, Band length: 3m****Order data**

Order number	462360 3
GTIN	3253561332180
Item class	46R

Description**Version:**

Tape measure with shock-resistant chromium-plated metal casing. Extra-strong tape with scale of the front and back faces. With locking function and automatic tape return. Tape fully coated with a protective layer for high abrasion resistance. Supplied with belt clip.

Technical description

Body length	57 mm
Body width	22 mm
Body height	60 mm
Tape width	12.7 mm
Standard	EG II
Calibration	G1
Type of product	Measuring tape

Services

CalibrationTape measure maximum length 5 m

026240 5