

BENNING**Phase tester, Type: VT1****Order data**

Order number	473282 VT1
GTIN	4014651200548
Item class	47A

Description**Version:**

For quick and easy phase testing at sockets, junction boxes, switches and lamps. Locates cable breaks in insulated cables.

Function:

IP40: Protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away, and offers no protection against water.

Application:

Phase testing, testing of insulated cables and testing for broken cables.

Standard:

DIN EN 61010-1.

Supplied with:

2 batteries No. 081561 size LR3.

Technical description

Voltage range AC	200 - 1000 V
Overvoltage category	CAT III 1000 V; CAT IV 600 V
IP Index of Protection	IP 40
Number of batteries contained	2
Power supply	Battery-powered
Article no of the battery / rechargeable battery fitted	081561 LR3
Material of the housing	ABS plastic
Type of product	Phase tester

Accessories

Alkaline-manganese batteries International size LR3

081561 LR3