

KERN
Crane scales type HCD, maximum weighing range: 300kg

Order data

Order number	479434 300
GTIN	4045761214170
Item class	47D

Description
Version:

Back-lit LCD display, easily read even from afar. Data hold function for retaining the display value. High mobility thanks to stable lightweight design. Battery lasts approx. 20 hours.

Supplied with:

Including remote control with 2 batteries No. 081561 size LR3. Scales including 4 batteries No. 081561 LR6.

Technical description

Scale divisions	100 g
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR3
Body depth	79 mm
Calibration	Price on request
Body width	194 mm
Error limit from maximum value	0.2 %

Overall length	276 mm
Body height	97 mm
Net weight	1.1 kg
maximum weighing range	300 kg
Operating temperature	0 - 40 °C
Power supply	Battery-powered
Display backlit	yes
Data storage key	yes
Battery working life	20 h
Type of product	Suspended scales / crane scales

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------