

KERN**Crane scales type HCD, maximum weighing range: 60kg****Order data**

Order number	479434 60
GTIN	4045761214163
Item class	47D

Description**Version:**

Back-lit LCD display, easily read even from afar. Data hold function for retaining the display value. High mobility thanks to stable lightweight design. Battery lasts approx. 20 hours.

Supplied with:

Including remote control with 2 batteries No. 081561 size LR3. Scales including 4 batteries No. 081561 LR6.

Technical description

maximum weighing range	60 kg
Error limit from maximum value	0.2 %
Scale divisions	20 g
Operating temperature	0 - 40 °C
Body depth	79 mm
Calibration	Price on request
Body width	194 mm

Body height	97 mm
Overall length	276 mm
Article no of the battery / rechargeable battery fitted	081561 LR3
Net weight	1.1 kg
Number of batteries contained	2
Power supply	Battery-powered
Display backlit	yes
Data storage key	yes
Battery working life	20 h
Type of product	Suspended scales / crane scales

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------