

**Garant**

**Workstation with electric height adjustment Load capacity max. 250 / 200 kg  
dark Eluplan worktop, Type: 2000**

**Order data**

Order number	920301 2000
GTIN	4062406261658
Item class	9GG

**Description****Version:**

Base frame with lift unit with cross braces for stabilisation at the side and rear. 50 mm thick worktop made of dark Eluplan. Work bench **without** side plates, not suitable for installing in a row.

**Colour:**

Height-adjustable feet in black, cross braces in RAL 7016 anthracite **powder-coated**.

**Recommendation:**

Light assembly work, sitting and standing.

**Note:**

Because of the maximum load capacity, only mobile casings should be used. Avoid attaching casings under the worktop. Further attachments would reduce the load capacity correspondingly. Delivered fully assembled.

**Technical description**

Height adjustment range (worktop surface) from – to	610 - 1200 mm
ComfortClose	no
Lifting speed	38 mm/s
Depth	750 mm
Worktop depth	750 mm
Worktop length	2000 mm

maximum load capacity	200 kg
Weight	115 kg
Width	2000 mm
Worktop thickness	50 mm
Workbench/desk load capacity - maximum distributed load (on wood)	200 kg
Plug type, input	F
Nominal voltage	250 V
Material thickness	1 mm
Type of height adjustment	electrical
Insert thickness	50 mm
Type of product	Work table