

Garant

**Workstation with electric height adjustment Load capacity max. 250 / 200 kg
dark Eluplan worktop, Type: 2000/S**

**Order data**

Order number	920301 2000/S
GTIN	4062406261665
Item class	9GG

Description**Version:**

Base frame with lift unit with cross braces for stabilisation at the side and rear. 50 mm thick worktop made of dark Eluplan. Work bench **with** side plates, suitable for installing in a row.

Colour:

Height-adjustable feet in black, cross braces in RAL 7016 anthracite **powder-coated**.

Recommendation:

Light assembly work, sitting and standing.

Note:

Because of the maximum load capacity, only mobile casings should be used. Avoid attaching casings under the worktop. Further attachments would reduce the load capacity correspondingly. Delivered fully assembled.

Technical description

Lifting speed	38 mm/s
Worktop thickness	50 mm
Depth	750 mm
Height adjustment range (worktop surface) from – to	720 - 1200 mm
Weight	119 kg
Worktop length	2000 mm

ComfortClose	no
Worktop depth	750 mm
maximum load capacity	200 kg
Width	2000 mm
Workbench/desk load capacity - maximum distributed load (on wood)	200 kg
Plug type, input	F
Nominal voltage	250 V
Material thickness	1 mm
Type of height adjustment	electrical
Insert thickness	50 mm
Type of product	Work table