

Garant

**Workstation with electric height adjustment Load capacity max. 350 / 300 kg
dark Eluplan worktop, Type: 2000**

**Order data**

Order number	920306 2000
GTIN	4062406261672
Item class	9GG

Description**Version:**

Base frame with lift unit with cross braces for stabilisation at the side and rear. 50 mm thick worktop made of dark Eluplan. Work bench **without** side plates, not suitable for installing in a row.

Colour:

Height-adjustable feet in black, cross braces in RAL 7016 anthracite **powder-coated**.

Recommendation:

Light assembly work, sitting and standing.

Note:

Because of the maximum load capacity, only mobile casings should be used. Avoid attaching casings under the worktop. Further attachments would reduce the load capacity correspondingly. Delivered fully assembled.

Technical description

Worktop depth	750 mm
Width	2000 mm
Weight	98 kg
Worktop thickness	50 mm
Worktop length	2000 mm
Depth	750 mm

Height adjustment range (worktop surface) from – to	610 - 1200 mm
Lifting speed	22 mm/s
maximum load capacity	300 kg
Workbench/desk load capacity - maximum distributed load (on wood)	300 kg
Nominal voltage	250 V
Plug type, input	F
Material thickness	1 mm
Type of height adjustment	electrical
Insert thickness	50 mm
Type of product	Work table