



Torx® key L-wrench, with knurling, Torx® profile: TX7



Order data

| | |
|--------------|---------------|
| Order number | 625037 TX7 |
| GTIN | 7610733281848 |
| Item class | 63D |

Description

Version:

L-shank; through hardened (hard and tough). PB Swiss Tools special steel combining maximum hardness with exceptional toughness. Surface nickel-plated and chrome-plated. Black tip.

Advantage:

The knurling to ISO 13444 type B increases the grip in wet or oily environments and thus enhances safety.

Technical description

| | |
|----------------------------|-------------------------------|
| Torx® profile | TX7 |
| Stock length | 93×19 mm |
| Manufacturer's designation | Safety L-wrench |
| Drive profile | Screwdriver for TORX® screws |
| Material | PB Swiss Tools special alloy. |
| Type of shank | angled |
| Surface | chrome-plated |
| Point | black |
| Ball point on the long arm | no |
| Type of product | Screwdrivers |

