

Office swivel chair with fabric backrest, Colour: BLACK



Order data

Order number	974285 BLACK
GTIN	4016849842967
Item class	96B

Description

Version:

Seat with soft comfort padding with base stitched at the side. Covering 100% polyester. Synchro-technology with automatic weight adjustment, can be locked in the front and rear seating position. With adjustable seat depth, seat angle and seat height. Supplied with height-adjustable armrests (2D). Universal rollers for hard and soft floors, Ø 650 mm star base of black plastic. Office swivel chair with soft breathable fabric backrest, with height-adjustable profiled lumbar support. Back partially plastic-covered.

Standard:

DIN EN 1335, Brandschutznorm EN 1021 Teil 1 und 2.

Technical description

Safe working load	120 kg
Synchro mechanism	yes
Colour of seat material	black
Seat depth adjustment range	60 mm
Base version	Set of castors

Material of base	Plastic
Backrest height	560 mm
Seat width	470 mm
Lumbar support	yes
Seat depth	470 mm
Armrest pair can be adjusted	yes
Version	with castors
Load capacity chair	120 kg
Star base Ø	650 mm
Height adjustment range	420 - 550 mm
Type of product	Office chair