

Electrically height-adjustable office desk Beech, Width: 2000 mm



Order data

Order number	974022 2000
GTIN	2050002041356
Item class	91Q

Description

Version:

Office desk with electric height adjustment using controls. Base of powder-coated welded steel frame. Mounted on the table surface by direct bolting on the frame and two asymmetrically arranged profile bearers. The entire leg area of the frame is clear of obstructions, so mobile drawer units up to 560 mm in height can be accommodated under the desk. Speed of travel for height adjustment 38 mm/s (unloaded). Noise level less than 50 dB. Rail with pad for 10 mm height adjustment. Supplied with approach protection by means of resistance measurement. Melamine desk top with beech-effect surface.

Standard:

DIN EN 527-1/-2/-3 für Grundkonstruktion, DIN 60335-1 elektr. Sicherheit.

Colour:

Base frame metallic grey **powder-coated**.

Insert thickness: 25 mm

Height adjustment range: 650 - 1300 mm

Width: 2000 mm

Depth: 800 mm

Worktop thickness: 25 mm

maximum load capacity: 70 kg

Weight: 75 kg

Technical description

Width	2000 mm
-------	---------

Height adjustment range	650 - 1300 mm
Worktop thickness	25 mm
Weight	75 kg
Depth	800 mm
maximum load capacity	70 kg
Type of height adjustment	electrical
Insert thickness	25 mm
Type of product	Office desk with electric height adjustment

Accessories

Acoustic partition wall Type 2000	974150 2000
Cable sleeve Length 1250 mm	974125 1250
PC-holder Type 3	974130 3
Folding cable duct suitable for table width 2000 mm	974120 2000
Under-desk modesty screen Metal suitable for table width 2000 mm	974111 2000
Under-desk modesty screen Wood suitable for table width 2000 mm	974110 2000
Cable pass-through Number of sleeves 2LR	974100 2LR
Cable pass-through Number of sleeves 1R	974100 1R
Cable pass-through Number of sleeves 1M	974100 1M
Cable pass-through Number of sleeves 1L	974100 1L