

Electrically height-adjustable office desk Beech, Width: 1600 mm



Order data

Order number	974022 1600
GTIN	2050002041349
Item class	91Q

Description

Version:

Office desk with electric height adjustment using controls. Base of powder-coated welded steel frame. Mounted on the table surface by direct bolting on the frame and two asymmetrically arranged profile bearers. The entire leg area of the frame is clear of obstructions, so mobile drawer units up to 560 mm in height can be accommodated under the desk. Speed of travel for height adjustment 38 mm/s (unloaded). Noise level less than 50 dB. Rail with pad for 10 mm height adjustment. Supplied with approach protection by means of resistance measurement. Melamine desk top with beech-effect surface.

Standard:

DIN EN 527-1/-2/-3 für Grundkonstruktion, DIN 60335-1 elektr. Sicherheit.

Colour:

Base frame metallic grey **powder-coated**.

Insert thickness: 25 mm

Height adjustment range: 650 - 1300 mm

Width: 1600 mm

Depth: 800 mm

Worktop thickness: 25 mm

maximum load capacity: 70 kg

Weight: 60 kg

Technical description

Weight	60 kg
--------	-------

Width	1600 mm
Height adjustment range	650 - 1300 mm
Depth	800 mm
maximum load capacity	70 kg
Worktop thickness	25 mm
Type of height adjustment	electrical
Insert thickness	25 mm
Type of product	Office desk with electric height adjustment

Accessories

Acoustic partition wall Type 1600	974150 1600
Cable sleeve Length 1250 mm	974125 1250
PC-holder Type 3	974130 3
Folding cable duct suitable for table width 1600 mm	974120 1600
Under-desk modesty screen Metal suitable for table width 1600 mm	974111 1600
Under-desk modesty screen Wood suitable for table width 1600 mm	974110 1600
Cable pass-through Number of sleeves 2LR	974100 2LR
Cable pass-through Number of sleeves 1R	974100 1R
Cable pass-through Number of sleeves 1M	974100 1M
Cable pass-through Number of sleeves 1L	974100 1L