



Combination spanner, Width across flats: 10mm



Order data

Order number	613800 10
GTIN	4013288212542
Item class	63F

Description

Version:

Drop-forged. With close tolerance jaw width.

Particularly suitable where space is tight. The combination of the 7.5° offset for the open jaws and the bi-hexagon geometry for the ring achieves a doubling of the application points. The small working arc of the open jaws allows the bolt head to be gripped every 15° of rotation.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome molybdenum steel, matt chrome-plated.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 613600

Technical description

Width across flats	metric
maximum ring height $h_{2\max}$	9 mm
Width across flats	10 mm
Spanner length L	125 mm
maximum jaw height h_1	5 mm
Manufacturer's designation	6003 Joker
Standard	DIN 3113 A

Standard	ISO 3318
Standard	ISO 7738
Manufacturing process	drop forged
Material	Chromium-molybdenum steel.
Surface	matt chrome-plated
Type of product	Spanner