

**Fabric adhesive tape UV-resistant, transparent, Width×length (mm× m):  
48X25****Order data**

Order number	083607 48X25
GTIN	4042448902030
Item class	08M

**Description****Version:**

The **tesa® 4665** is **UV-resistant** for 52 weeks and in addition is **weather-resistant**. It is thus ideal as an outdoor adhesive tape.

**Note:**

The specified "best before" date for tesa® products is in relation to compliance with the specified storage guidelines.

**Technical description**

Fabric fineness	30 mesh
Colour	transparent
Adhesive strength on steel	0.9 N/mm
Backing material	Fabric
Storage temperature	15 - 35 °C
Storage humidity	50 - 70 %

Tensile strength	4.3 N/mm
Stretch capability	27 %
Width	48 mm
Adhesive	Synthetic rubber
Type of adhesive tape	single-sided
Thickness	0.215 mm
temperature-resistant up to	95 °C
Manufacturer's designation	4665
Liner present	no
Length	25 m
Product name attribute	transparent
Type of product	Adhesive tape