

Garant GRIDLINE

Workbench, left side 3 drawers, centre open, right side door and 1 drawer, Bamboo worktop, 20×20G, Worktop length: 2000mm



Order data

Order number	921151 2000
GTIN	4062406262181
Item class	9GG

Description

Version:

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Feet with plastic pads, do not damage the floor.

Centre part with recessed open housing for ergonomic posture.

Drawer bodies always RAL 7035 light grey, **powder coated**. Variable colours for the drawer fronts. No surrounding ledges, thereby allowing optimum cleaning and full availability of the area for drawer dividers (boxes, rigid foam inlays, slotted partitions). Drawer runner mountings at 25 mm intervals.

Locking system with 5-pin cylinder locks and modular barrels. Compatible with integrated locking systems.

Fitted with:

Drawer front height (left) mm: 125, 200, 300

Drawer front height (right) mm: 125

Door height (right) mm: 475

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite grey, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Door height (right)	375 mm
Weight	153 kg
Worktop thickness	50 mm
Support cabinet depth	700 mm
Support cabinet width	1900 mm
Series	Ready-to-go
Drawer usable depth in G	20
Height	950 mm
Drawer body usable height	625 mm
Drawer usable width in G	20
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer usable area in G	20×20
Worktop depth	750 mm
Drawer usable depth	500 mm
Drawer usable width	500 mm
Worktop length	2000 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Slide handle for GridLine Type KO12	914226 KO12
Drawer Drawer front height 200 mm	927800 200
Drawer Drawer front height 300 mm	927800 300
Drawer Drawer front height 125 mm	927800 125