

**Fabric adhesive tape Set, 3 pieces, pink, Width×length (mm× m): 50X25****Order data**

| | |
|--------------|---------------|
| Order number | 083617 50X25 |
| GTIN | 4042448180858 |
| Item class | 08M |

Description**Version:**

The **tesa® 4671** has a backing fabric of rayon, **is non-reflective, is fluorescent** and is suitable for virtually **any sort of application**. It can easily be torn by **hand**, can be **removed without leaving residues**, bonds to **rough surfaces** and **can be written on**.

With the tesa® 4671 fabric tape in neon colours, you can master various tasks safely and reliably – particularly when marking various elements or in the event field!

The tesa® 4671 fabric tape is available in fluorescent neon colours and is often used by specialists for visible marking of various elements or as part of events. It is suitable for a wide variety of applications such as marking, fixing, securing or binding. tesa® 4671 can be easily torn by hand, is easy to mark, does not reflect and can be shaped. The combination of acrylate-coated fabric and adhesive made from natural rubber ensures high abrasion resistance. The fabric tape can be removed leaving no residue and is available in the following colours: neon green, neon yellow, neon orange and neon pink.

Note:

The specified "best before" date for tesa® products is in relation to compliance with the specified storage guidelines.

Technical description

| | |
|-----------------------------|----------------|
| Liner present | no |
| Stretch capability | 9 % |
| Length | 25 m |
| Tensile strength | 7 N/mm |
| Type of adhesive tape | single-sided |
| Manufacturer's designation | 4671 |
| Storage humidity | 50 - 70 % |
| Width | 50 mm |
| Fabric fineness | 120 mesh |
| temperature-resistant up to | 140 °C |
| Adhesive | Natural rubber |
| Backing material | Fabric |
| Colour | pink |
| Thickness | 0.28 mm |
| Adhesive strength on steel | 0.35 N/mm |
| Storage temperature | 15 - 35 °C |
| Product name attribute | pink |
| Type of product | Adhesive tape |