

**Rechargeable LED pen light, Type: 175****Order data**

Order number	081577 175
GTIN	4062406262044
Item class	02A

Description**Version:**

Rechargeable LED pen light with steplessly dimmable main beam and additional spotlight function. Strong magnet in the lamp base.

Function:

IP30: Protected against penetration by foreign bodies with $\varnothing > 2.5$ mm, however tools and wires should be kept away, and offers no protection against water.

Supplied with:

Including USB charging cable.

Technical description

Battery voltage	3.7 V
Bulb	LED module
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	1
Weight	77 g

Overall length	175 mm
Battery capacity	0.8 Ah
Illumination time	2 - 16 h
ATEX zone	no
Illumination	20 - 200 lm
IP Index of Protection	IP 30
Overall width	23 mm
Power supply	Rechargeable battery-powered
Type of product	Flashlight