



## TMSERROR, Type: 4ULTRA



### Order data

Order number	081590 4ULTRA
GTIN	4013674144679
Item class	08C

### Description

#### Version:

Microprocessor-controlled charging and servicing stations for battery cells with **individual channel monitoring** and battery fault detection. Status display for each charging slot, automatic charging switch-off, overload protection and **trickle charging**. Input voltage 100–240 V. With LC display for detailed monitoring of the charging process and additional acoustic feedback.

#### Application:

**NiMH/NiCd battery charging points:** 1-4 × Micro AAA / Mignon AA or 1-3 × Baby C or 1-2 × Mono D.

**Li-Ion battery charging points:** 1-4 × 18650, 18500, 17670, 16340, 14500 etc. or 1-3 × 26650, 26500, 25500, 22650 or 1-2 × 3265.

#### Attention:

German version. Order free UK adapter plug No. 08 1172\_GB

### Technical description

maximum charging current	2 A
Length	170 mm
Height	37.5 mm
Width	110 mm
Maximum number of charging points	4

suitable battery - supplier / battery type / voltage	Type CAS 18 V
Number of charging slots for USB	1
Nominal voltage	100 - 240 V
Interface	Digimatic interface
Type of product	Battery charger