

**LED torch, Type: P3R****Order data**

Order number	081467 P3R
GTIN	4058205009362
Item class	04B

Description**Version:**

LED lenses are amongst the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All lamps are equipped with focussable lamp head. Compact torches in bar format or key fob format.

· **Optionally as a disposable battery or rechargeable battery version.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with charging station and USB charging cable.

IP Index of Protection: IP 54

ATEX zone: no

Illumination: 140 lm

Illumination step 2: 20 lm

Working life: 2.5 h

Lighting life stage 2: 6 h

Advanced Focus System (AFS): yes

Technical description

Head Ø	20 mm
Illumination	140 lm
Manufacturer's designation	P3R

ATEX zone	no
Power supply	Rechargeable battery-powered
Bulb	LED module
Advanced Focus System (AFS)	yes
Type of rechargeable battery	Lithium-ion
Illumination step 2	20 lm
Overall length	102 mm
Weight	42 g
Number of rechargeable batteries contained	1
Smart Light Technology (SLT)	no
IP Index of Protection	IP 54
Working life	2.5 h
Lighting life stage 2	6 h
Type of product	Flashlight