



LED torch, Type: P3



Order data

Order number	081467 P3
GTIN	4058205009393
Item class	04B

Description

Version:

Compact torches in bar format or key fob format.

· **Optionally as a disposable battery or rechargeable battery version.**

LED lenses are amongst the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All lamps are equipped with focussable lamp head.

Function:

IPX4: Protected against splashed water from all directions, but without any protection against foreign bodies or touching.

IP Index of Protection: IP X4

ATEX zone: no

Illumination: 25 lm

Working life: 6 h

Advanced Focus System (AFS): yes

Smart Light Technology (SLT): no

Number of batteries contained: 1

Technical description

ATEX zone	no
Battery type	Micro, AAA
Smart Light Technology (SLT)	no
Head Ø	19 mm

Number of batteries contained	1
Power supply	Battery-powered
IP Index of Protection	IP X4
Working life	6 h
Advanced Focus System (AFS)	yes
Manufacturer's designation	P3
Weight	35 g
Bulb	LED module
Illumination	25 lm
Overall length	90 mm
Type of product	Flashlight

Accessories

Alkaline-manganese batteries International size LR3	081551 LR3
Alkaline-manganese batteries International size LR3	081552 LR3
Alkaline-manganese batteries International size LR3	081553 LR3
Alkaline-manganese batteries International size LR3	081554 LR3
Lithium-metal batteries International size LR3	081559 LR3
Alkaline-manganese batteries International size LR3	081561 LR3