



## Straight edge with burnished finish in a case, Length: 500mm



### Order data

Order number	460100 500
GTIN	4062406264338
Item class	42G

### Description

#### Version:

Hardened, ground, and precision lapped straight edge. Wedge shaped cross section tapering to a point for inspection even in corners, grooves, cut outs etc. With plastic insulated handle to protection against body heat.

Made of aged special steel, both bevels burnished (anti-glare).

#### Note:

The straightness tolerance of the measuring edge refers to a displacement range of  $\pm 15^\circ$  to the symmetry plane.

### Technical description

Length	500 mm
Straightness tolerance of the measuring edge	0.004 mm
Standard	DIN 874
Material	aged special steel
Surface chamfer	burnished (non-glare)
Packaging	Wallet
Calibration	F6
Type of product	Straight edge

### Services

CalibrationStraight edge maximum length 500 mm	026000 500
--	------------

DAkkS calibration Straight edge maximum length 500 mm

026010 500