

**MARPOSS**
**DUO measured value display unit, Type: DUO**

**Order data**

Order number	434735 DUO
GTIN	2050002040861
Item class	43D

**Description**
**Version:**

Compact measured value display unit with 4.3-inch touch screen/colour display and measured value memory function. Connection for 2 inductive contact points (switchable between half-bridge or full-bridge). Device also compatible with Tesa contact points. Up to 2 features can be displayed at the same time. Data export in CSV format via the USB interface.

**Function:**

- **Dynamic measured value functions: Max, Min, Max-Min, (Min-Max)/2, average.**
- **Three-colour bar display and digital measured value display.**
- **2 circuit inputs and 2 circuit outputs, potential-free (for instance for measured value uploading, good/reject).**
- **Scaling is adjusted automatically to suit the tolerance limit.**

**Application:**

As display for simple measurement tasks (+A, -A) and calculation based on both results (such as A+B, A-B, 0.5A+B). For use in the workshop and production.

**Supplied with:**

Including USB power adaptor, base.

**Technical description**

Weight	1 kg
Length	130 mm
maximum resolution	0.01 $\mu\text{m}$
Width	95 mm
Height	50 mm
Measuring range	$\pm 1$ up to $\pm 10000 \mu\text{m}$
Power supply	Mains-powered
Reversible reading	mm / inch
Interface	Digimatic interface
Type of product	Display unit