

3M**VHB™ adhesive tape, black, Width×length (mm× m): 19X8**

Order data

Order number	083782 19X8
GTIN	4054596308619
Item class	08M

Description

Version:

Double-sided high-performance **adhesive tape** of pure acrylate adhesive (VHB) for permanently strong bonds. High instant tack, high resistance to temperature, weather, UV and solvents. Excellent sealing function, vibration-damping.

The **3M™ 5952** means reliability right across the board. It offers optimum adaptability to the surfaces to be bonded. This feature permits even thin and structured surfaces to be joined without any sort of stress.

Note:

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Further 3M™ VHB™ tapes in different thicknesses and lengths are available on request.

Adhesive: Acrylate

Length: 8 m

Width: 19 mm

Thickness: 1.6 mm

Technical description

Adhesive strength on steel	5.5 N/mm
Storage humidity	50 %
Type of adhesive tape	double-sided
Colour	grey
Material of covering	Paper
Width	19 mm
Manufacturer's designation	5962F
Length	8 m
Stretch capability	300 %
Adhesive	Acrylate
"Best before" date	12 mo
Application	Sealing
Application	Attaching
Application	Masking
Application	Assembly
temperature-resistant up to	120 - 150 °C
Special features	clings well
Special features	damping
Special features	moisture-resistant
Storage temperature	20 °C
Thickness	1.6 mm
Product name attribute	black
Type of product	Adhesive tape